

RE-HEALING™ RF1-AG, 1% FOAM CONCENTRATE

CONCENTRATES



Description

RE-HEALING™ RF1-AG, 1% foam concentrate from SOLBERG® is an innovative environmentally sustainable fluorosurfactant and fluoropolymer-free foam concentrate used to effectively extinguish Class B hydrocarbon fuel fires. Proportioned at 1% solution, RE-HEALING RF1-AG foam concentrate can be used in fresh and salt water. RE-HEALING RF1-AG foam concentrate possesses excellent burn back resistance due to its remarkable flow and rapid resealing characteristics. RE-HEALING RF1-AG foam concentrate is formulated using a new high performance synthetic foam technology to replace traditional AFFF, FFFP foam concentrates and older protein and fluoroprotein foams.

Application

RE-HEALING RF1-AG foam concentrate is intended for use on Class B hydrocarbon fuel fires. It is not intended for use on Class B polar solvent fuels. The foam can be used to prevent re-ignition of a liquid spill and control hazardous vapors. On Class A fuels, RE-HEALING RF1-AG foam will improve extinguishment in

deep-seated fires. Foam discharge devices such as air aspirating, as well as non-air aspirating equipment can be used to obtain maximum results. The product is mixed 1 part foam concentrate to 99 parts water. It may also be used as a 1% pre-mix solution. RE-HEALING RF1-AG foam is compatible with most dry powder (chemical) agents.

Performance

Fire Performance

RE-HEALING RF1-AG foam concentrate has been tested to and meets the fire performance test criteria of European Standard EN 1568 Part 3 (latest edition).

Foam Proportioning

RE-HEALING RF1-AG foam concentrate can be proportioned at the proper foam solution percentage using common foam proportioning devices such as:

- Eductors
- Inline balanced pressure proportioners
- Ratio controllers
- Self-educting nozzles

Typical Physical Properties at 77 °F (25 °C)

Appearance:	Clear, yellow-orange liquid
Freezing Point:	-11 °F (-24 °C) <i>(No quality loss after thawing)</i>
Maximum storage temp:	122 °F (50 °C)
pH:	7.0 - 8.5
Refractive index:	1,4580 - 1.4680
Specific gravity:	1,120 - 1,130
Viscosity:	<20 cSt*
Sediments:	<0.05%

*Cannon-Fenske Viscometer

Storage

The storage temperature range for RE-HEALING RF1-AG foam concentrate is -11 °F to 122 °F (-24 °C to 50 °C). When stored in original containers or in manufacturer recommended equipment and within the specified temperature range, the shelf life is 20 years.

Compatibility

RE-HEALING RF1-AG foam concentrate should not be mixed with other foam concentrates. For questions about compatibility or mixing, consult Solberg Technical Services.

SOLBERG is a member of PERIMETER SOLUTIONS, a global producer of leading fire retardant, gel and foam brands with a singular purpose: revolutionize the course of fire suppression technology with safer, more effective and more sustainable solutions. Together, we are Moving Industries Forward by Redefining Fire Suppression. www.solbergfoam.com



Materials of Construction Compatibility

RE-HEALING RF1-AG foam concentrate is compatible with multiple materials of construction such as carbon steel, stainless steel, brass, polyethylene and PVC. Galvanized steel should not be used in direct contact with the foam concentrate. For questions about materials of construction compatibility, consult Solberg Technical Services.

Inspection

RE-HEALING RF1-AG foam concentrate or pre-mix solution should be inspected annually per

National Fire Protection Association (NFPA) Standards 11 and 25. A sample of the foam concentrate should be sent to the manufacturer for quality conditioning testing in accordance to NFPA 11.

Environmental Information

RE-HEALING foam concentrates are fluorosurfactant, fluoropolymer-free products for use on Class B hydrocarbon fuels with no environmental concerns for persistence, bioaccumulation or toxic break down.

Certifications

SOLBERG manufactured products are thoroughly inspected and undergo rigorous quality control tests. These evaluations analyze the foam’s physical parameters as well as the finished product’s fire performance. A Certificate of Analysis (CoA) is issued with every batch.

RE-HEALING RF1-AG foam concentrate is European Standard EN 1568 Part 3 Approved.

Ordering Information

RE-HEALING RF1-AG foam concentrate is available in pails, drums, totes and bulk quantities.

PART NO.	DESCRIPTION	APPROXIMATE SHIPPING WEIGHT	APPROXIMATE CUBE
20840	RE-HEALING RF1-AG, 1% - 5 gallon (20 litre) pail	45 lb (21 kg)	1.25 ft ³ (0.04 m ³)
20841	RE-HEALING RF1-AG, 1% - 55 gallon (200 litre) drum	495 lb (224 kg)	11.83 ft ³ (0.33 m ³)
20842	RE-HEALING RF1-AG, 1% - 265 gallon (1000 litre) tote	2465 lb (1118 kg)	50.05 ft ³ (1.42 m ³)
20843	RE-HEALING RF1-AG, 1% - bulk	Call Customer Services	



NOTICE: Perimeter Solutions makes no representations or warranties as to the completeness or accuracy of the information included herein. The information contained herein is not intended to provide regulatory, legal or expert advice relating to the products, its application or uses. Nothing contained herein is to be construed as a recommendation to use any product, process, equipment or formulation in conflict with any industrial property or intellectual property rights, and Perimeter Solutions makes no representation or warranty, express or implied, that the use thereof will not infringe on any industrial property or intellectual property rights. NO REPRESENTATIONS OR WARRANTIES, EITHER EXPRESSED OR IMPLIED, OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY OTHER NATURE ARE MADE HEREUNDER WITH RESPECT TO THE INFORMATION CONTAINED HEREIN.

SOLBERGFOAM.COM

FORM NUMBER F-2016003-2

COPYRIGHT © 2016. ALL RIGHTS RESERVED. SOLBERG® AND RE-HEALING™ ARE TRADEMARKS OF PERIMETER SOLUTIONS LP OR ITS AFFILIATES.

PERIMETER SOLUTIONS
THE SOLBERG COMPANY
1520 Brookfield Avenue
Green Bay, WI 54313
USA
Tel: +1 920 593 9445

PERIMETER SOLUTIONS
AUXQUIMIA S.A.U.
Polígono de Baiña, Parcela 23
33682 Mieres (Asturias)
Spain
Tel: +34 985 24 29 45

PERIMETER SOLUTIONS
SOLBERG ASIA PACIFIC PTY LTD
3 Charles Street
St. Marys NSW 2760
Australia
Tel: +61 2 9673 5300